



# ASM 310, universal voltage




# ASM 310



## ASM 310, universal voltage

- Oil free pumping system, roughing capacity 1.7 m<sup>3</sup>/h
- Ultralight, only 21 kg (46 lbs) and easy to move
- Large bright color touchscreen with graphics functionality
- Intuitive and customizable menu
- Recording capacities with data export through dedicated USB port

## Dimensions



<b>Technical Data</b>	<b>ASM 310, universal voltage</b>
Pumping speed backing pump	1.7 m <sup>3</sup> /h
Pumping speed for He	1.1 l/s
Test method	Vacuum leak detection   Sniffing leak detection
I/O interfaces	RS-232
Interface: Connection, device side	Standard 15 pins I/O
Minimum detectable leakage rate for helium (vacuum leak detection)	$1 \cdot 10^{-13}$ Pa m <sup>3</sup> /s
User interface	Graphic color touch screen (detachable)
Response time (Sniffing leak detection)	< 1 s
Backing pump capacity	1.7 m <sup>3</sup> /h
Operating temperature	10 – 40 °C
Input voltage(s)	90 – 240 V AC, 50/60 Hz
Emission sound pressure level (EN ISO 2151)	<45 dB(A)
Start-up time (20°C) with calibration	3.5 min
Start-up time (20°C) without calibration	2 min
Pumping speed for He	1.1 l/s
Minimum detectable leakage rate for helium (sniffing leak detection)	$1 \cdot 10^{-8}$ Pa m <sup>3</sup> /s   $7.5 \cdot 10^{-8}$ Torr l/s   $1 \cdot 10^{-7}$ mbar l/s
Weight	21 kg   46.3 lb
Detectable gases	<sup>4</sup> He   <sup>3</sup> He   H <sub>2</sub>
Dimensions (L x W x H)	350 x 254 x 415 mm
Power consumption max.	300 W
Backing pump	With oil-free backing pump
Weight	21 kg
Connection flange (in)	DN 25 ISO-KF

<b>Order number</b>	<b>ASM 310, universal voltage</b>
ASM 310, universal voltage	BSAA0200MM9A

## Your Success. Our Passion.

We give our best for you every day –  
worldwide!

Are you looking for an optimum vacuum solution?

Talk to us:  
Pfeiffer Vacuum GmbH  
Germany  
T +49 6441 802-0

Or scan the barcode, to visit our web page:



<https://webportal.pfeiffer-vacuum.com/global/en/contact>



Errors and/or changes excepted. - 11/1/2024

Follow Us On Social Media  
#pfeiffervacuum



[www.pfeiffer-vacuum.com](http://www.pfeiffer-vacuum.com)

**PFEIFFER**  **VACUUM**